



DOSATRON®

An Ingersoll Rand Business

CLICK CHARTS

Only to be used as a guideline

3 GPM (11 LPM) D07RE5 - D07RE125		
Clicks per 15 seconds		
CLICKS	GPM	LPM
4	0.5	2
8	1	4
12	1.5	6
16	2	8
20	2.5	10
24	3	11

9 GPM (34 LPM) D14MZ520		
Clicks per 15 seconds		
CLICKS	GPM	LPM
3	1	4
10	3	11
19	5	19
22	7	27
31	9	34

7 GPM (26.5 LPM) D128R		
Clicks per 15 seconds		
CLICKS	GPM	LPM
4	1	4
9	2	8
15	3.5	13
22	5	19
31	7	27

11 GPM (42 LPM) D25RE2 - D25RE5 - D25F D25F1 - D25RE09 - D25RE10*		
Clicks per 15 seconds		
CLICKS	GPM	LPM
4	1	4
15	3	11
22	5	19
31	7	27
39	9	34
46	11	42

*D25RE10 flows up to 8.8 GPM
which equals 36 clicks

11 GPM (42 LPM) DM11F - DM11RE3		
Clicks per 2 minutes		
CLICKS	GPM	ml
1	0.02	75
2	0.05	189
3	0.1	379
Clicks per 1 minute		
CLICKS	GPM	LPM
3	0.2	1
6	0.4	2
Clicks per 15 seconds		
CLICKS	GPM	LPM
2	0.5	2
4	1	4
12	3	11
24	6	23
34	9	34
40	11	42



DOSATRON®

An Ingersoll Rand Business

CLICK CHARTS

Only to be used as a guideline

14 GPM (53 LPM) D14MZ2 - D14MZ5 D14MZ10 - D14MZ1000 - D14MZ3000 - D14TMZ5 - D14TMZ10 - D14TMZ3000		
Clicks per 15 seconds		
CLICKS	GPM	LPM
2	0.5	2
3	1	4
10	3	11
21	6	23
35	10	38
49	14	53

20 GPM (76 LPM) D45RE3 - D45RE8 - D45RE15		
Clicks per 15 seconds		
CLICKS	GPM	LPM
2	1	4
7	3	11
12	5	19
25	10	38
37	15	57
45	20	76

40 GPM (152 LPM) D8RE2 - D8R5 - D8RE3000		
Clicks per 15 seconds		
CLICKS	GPM	LPM
1	2	8
4	5	19
9	10	38
18	20	76
27	30	114
36	40	152

40 GPM (152 LPM) D40MZ2 - D40MZ5 - D40MZ1000 - D40MZ3000		
Clicks per 15 seconds		
CLICKS	GPM	LPM
1	0.9	3.6
5	4.5	17
11	10	38
22	20	76
33	30	114
44	40	152

100 GPM (379 LPM) D20S		
Clicks per 15 seconds		
CLICKS	GPM	LPM
2	6	23
4	12	45
9	25	95
18	50	190
36	100	379